

SPECIFICATIONS

Device Name	Iris			
Laser	Nd : YAG			
Beam Profile	Super Hive Flat mode (top hat mode)			
Mode	1064	532	SLP	PTP Blue Toning
Pused Energy[mJ]	1600	500	2200-3000	1600
Wavelength[nm]	1064	532	1064	1064
Pulse Width	5-10ns	5-10 ns	300 ms	5-10ns
Spot[mm]/ Repetition[Hz]	2-10 / 1-10	2-10 / 1-10	2-10 / 1-10	2-7 / 10-15 8-9 / 10-12 10 / 10
Display	10.2" wide panel and jog dial smart panel			
Auto Management	Ethernet, WIFI, WCDMA FOR EASY MAINTENANCE SUPPORT			
Memory	User programmable 8 memories to save and load parameters			
Noise Level	50dB (patent cooling system) FOR LOW NOISE OPERATION			
Spot Size	Auto sensing zoom collimated handpiece (2 ~ 10mm)			
Lamp Life Time	10,000,000 shot or more			
Electrical Requirements	220-230VAC, 15A , 50Hz or 60Hz			
Dimensions(mm)/Weight	295(W) x 740(L) x 973(H) , 70Kg			



IRIS

Q SWITCHED ND : YAG LASER

WHAT **YOU** GET?
WILL GET:

- PERFECT TONING TREATMENTS
- HIGH PEAK POWER
- ENOUGH POWER CONTROL
- TRUE 15 Hz
- TRUE MAXIMUM ENERGY
- VARIOUS PTP MODES
- EASY INSTALLATION
- EASY MAINTENANCE
- BEFORE SERVICE
- REMOTE ASSISTANTS
- SYSTEM MONITORING



IRIS[®]

PTP BLUE TONING THERAPY

BLUESCOPE
company



Lana Medical Company
Kingdom of Saudi Arabia. Riyadh, Al Malaz
Prince Abdul Muhsin St. P.O.Box 245200
Zipcode 11312
Tel: +966 11 475573 Fax: +966 11 4755579

Email: info@lanamedical.com
www.lanamedical.com

Riyadh - Jeddah - Dammam - Abha



ISO 9001
ISO 13485



شركة لانا الطبية

Lana Medical Company



lanamedicalcompany




lanamedical



@lanamedical

TRUE MAXIMUM ENERGY

The maximum energy test with a 9 ϕ rod and super hive flat lens at the end of the handpiece unlike other machines



Advance Laser Optic Parts




TRUE 15 Hz

Power control technology supports true 15Hz all the time as much as possible without any energy variation.




True 15 Hz

PTP BLUETONING TECHNOLOGY (6:4)



Bluetoning controls the 1st and 2nd Q energy rate for each skin types and user preferences in the world to give dramatic treatment results.



THE WORLD FIRST CENTRAL MONITORING SYSTEMS

1. Auto alert system
2. Central monitoring system
3. Remote service system
4. Auto upgrading system



EASY HANDLING

Soft buttons and physical button with a jog dial provide user conveniences with various short cut menus



Jog Dial



Short Cut Keys

INTUITIVE GRAPHIC INTERFACE (IGI)

Users find out how to use intuitively without manual according to Iris' graphic user interface (IGI)



Basic GUI



Fractional GUI

EASY MAINTENANCE & WARRANTY

Iris has a slot type circuit electronic power system like a normal PC and it has auto calibration mode for handpieces




Auto-Calibration



Circuit Slots

NO NOISE WITHOUT WATER TANK & FAN

Iris doesn't have a plastic water tank with the patented technology for cooling system. It doesn't have loud noise.



No Water Tank



No Fan

INDICATIONS

Iris has proven technology and power treatments with toning, whitening, peeling and also wide range of other indications for all skin types

- PTP Bluetoning
- Tattoo Removal
- Freckle
- Abnom
- Nevus of OTa
- Inflammatory Acne
- Soft Peel (&SLP Mode)
- Cafe-au-lait

Treatments Before & After

